

Detailed scanning parameters of Supplementary Material S1 1.5T and 3.0T magnetic resonance equipment

		1.5T		3.0T			
		Signa HDe	Magnetom Avanto	Vantage Titan	Ingenia	Signa Pioneer	Discovery MR 750w
T1WI	TR	460ms	400ms	450ms	507ms	1929ms	400ms
	TE	12.6ms	8.7ms	12.0ms	7.5ms	23ms	20.4ms
T2WI	TR	3540ms	3400ms	3000ms	3000ms	4151ms	2000ms
	TE	130.2ms	84ms	90ms	80ms	134ms	76.5ms
层厚		3mm	3mm	3mm	2mm	2mm	2mm
层 间 距		3mm	3.3mm	3.5mm	2mm	2.5mm	1mm
矩阵		288x192	256x197	320x224	272x212	288x256	288x256
FOV		200x200mm	180x180mm	220x220mm	200x200mm	180x180mm	200x200mm
翻 转 角		90°	90°	90°	100°	111°	90°

。